



■ Vers. 735




■ Vers. 735




■ Vers. 516+429

SCHEMATICS



COMPOSITION EXAMPLES



TECHNICAL INFORMATION

	COVERING	Leather ☒	Soft Cover ☒			
	FILLING	Arms ☐ Fiber ☒ Foam ☐ Feather/Fiber Mix ☐ Feather	Seat cushion ☐ Fiber ☒ Foam ☐ Feather/Fiber Mix ☐ Feather	Back cushion ☐ Fiber ☒ Foam ☐ Feather/Fiber Mix ☐ Feather		
	COMFORT	Standard Comfort ☒	Firm Comfort ☒			
	FUNCTION	Bed ☐	Electric motion ☒	Motion ☐	Recliner ☐	Sliding ☒
	VISUAL APPEARANCE*	Low ☐	Medium ☐	High ☒		
	LEGS	Castors ☐	Metal ☐	Plastic ☐	Upholstered ☐	Wood ☐

VISUAL APPEARANCE

The product may reveal various wrinkles due to the combination of Elasticity of the covering, characteristics of the interior construction and the design of the product.

 Low

 Medium

 High

Products with Visual Appearance listed as High or Medium would require higher degree of care, where seats and back cushions may require fluffing and plumping more often than Products with Visual Appearance listed as Low.

NOTES

- Available in leather (TG only) or fabric.
- Pixel is an extremely versatile and innovative model where you can unleash your creativity in choosing different combinations of coverings between leather and fabric.
- Available in leather and fabric with optional contrast piping.
To be ordered with 2 coverings:
 - 1st Covering = Sofa/Bed
 - 2nd Covering = Piping
- When in leather (3 combo possibilities):
 - 1st and 2nd covering can be ordered in leather with same category.
 - 1st covering in leather and 2nd covering in fabric by selecting any color from the article Brezza.
 - 1st covering in leather (any category) and 2nd covering in leather by selecting any color from the article Le Mans.
- When in fabric (3 combo possibilities):
 - 1st and 2nd covering can be ordered in fabric with same category.
 - 1st covering in fabric and 2nd covering in leather by selecting any color from the article Le Mans.
 - 1st covering in fabric (any category) and 2nd covering in fabric by selecting any color from the article Brezza.

NOTES

- **SLIDING ADJUSTABLE BACKRESTS:** The backrest has a unique manual sliding system that can customize your comfort by increasing or decreasing the seat depth as you wish. The different positions of the backrest assist your preferable way to relax. The backrest operates as follows: At first you need to slide the backrest all the way to the back, to then slide it forward, finding the best position you want to keep it fixed, for back support. The backrest can have 20 positions.
- **ADJUSTABLE ARMS:** the arms are equipped with a manual ratchet mechanism that you can adjust:
 - for major arm support during formal seating.
 - for extra head support, in case you would like to lay down, in horizontal position.
- Its versatility includes two new elements that can be smartly used to complement your configurations:
 - a “self-standing backrest” (vers. 436)
 - a “self-standing armrest” (vers. 437)

Both are independent versions that “self-stand” thanks to a carefully studied weight placed internally in their base. You can feel free to move them around and place them as needed on the seating surface to easily provide back and arm support.

- **MANUAL & POWER SLIDING OPTIONS:**
 - Manual Sliding Versions: 516-517-492-493-731-732-735
 - Power Sliding Versions: 616-617-727-728-729-730-743

POWER SLIDING MECHANISM allows the backrest to move forward or backward changing the depth of the seat. This mechanism is activated by two touch buttons placed on the seat.
- A handle positioned on the lower section allows for smooth sliding adjustment of the backrest
- To allow modularity, the single elements can be put together thanks to the rubber stops under the legs.
- 212 version to be used only as a chaise longue while the 429 as a rectangular corner. These versions have same dimensions and look similar, but they differ from each other by the stitching.
 - > 429 version has extra stitching placed on the short side.
 - > 212 version has no stitching on all sides.
- A battery pack can be ordered with its own version code 830. For order entry please use XX for category and XXX for cover code. In order to optimize the duration of the battery, it is suggested to order one per each motion seat.